

Trane Rubber Isolator

FOR TTK



| DESCRIPTION | SIZE | LIST PRICE |
|--|------------|------------|
| Rubber Isolator Kit for TTK512-524 (4 pieces/set) | TT7745E-SP | 100 |
| Rubber Isolator Kit for TTK524LB5-060 (4 pieces/set) | TT7745C-SP | 100 |

Spring Isolator



OSM (แบบตั้ง)



USH (แบบแขวน)

SPRING แบบตั้ง (OSM)

| MODEL | P/N | RATE CAP | | MOUNT | | SPRING | | | LIST PRICE |
|------------|-------------|----------|------|---------|------------|------------|----|-----|------------|
| | | KGS | LBS | KG / MM | LBS / INCH | COLOR CODE | OD | HT | |
| OSM-A -10 | N/A | 10 | 22 | 0.4 | 22 | Gray | 44 | 76 | 1,200 |
| OSM-A -25 | N/A | 25 | 55 | 1 | 55 | Orange | 44 | 76 | 1,200 |
| OSM-A -50 | 70-OTHR0261 | 50 | 110 | 2 | 110 | Red | 44 | 76 | 1,200 |
| OSM-A -100 | 70-OTHR0092 | 100 | 220 | 4 | 220 | Blue | 44 | 76 | 1,200 |
| OSM-A -150 | 70-OTHR0043 | 150 | 330 | 6 | 330 | Yellow | 44 | 76 | 1,300 |
| OSM-B -100 | 70-OTHR0057 | 100 | 220 | 4 | 220 | Green | 60 | 105 | 1,300 |
| OSM-B -150 | N/A | 150 | 330 | 6 | 330 | Brown | 60 | 105 | 1,300 |
| OSM-B -200 | N/A | 200 | 440 | 8 | 440 | White | 60 | 105 | 1,400 |
| OSM-B -300 | 70-OTHR0188 | 300 | 660 | 12 | 660 | Orange | 60 | 105 | 1,400 |
| OSM-B -400 | N/A | 400 | 880 | 16 | 880 | Blue | 60 | 105 | 1,500 |
| OSM-C -350 | N/A | 350 | 770 | 14 | 770 | Black | 73 | 105 | 1,800 |
| OSM-C -500 | N/A | 500 | 1100 | 20 | 1100 | Green | 73 | 105 | 2,000 |
| OSM-C -600 | N/A | 600 | 1320 | 24 | 1320 | Orange | 73 | 105 | 2,200 |
| OSM-C -750 | N/A | 750 | 1650 | 30 | 1650 | Brown | 73 | 105 | 2,300 |

SPRING แบบแขวน (USH)

| MODEL | P/N | RATE CAP | | MOUNT | | SPRING | | | LIST PRICE |
|------------|--------------|----------|------|---------|------------|------------|----|-----|------------|
| | | KGS | LBS | KG / MM | LBS / INCH | COLOR CODE | OD | HT | |
| USH-A -10 | N/A | 10 | 22 | 0.4 | 22 | Gray | 44 | 76 | 1,200 |
| USH-A -25 | 690411120001 | 25 | 55 | 1 | 55 | Orange | 44 | 76 | 1,200 |
| USH-A -50 | 70-OTHR0211 | 50 | 110 | 2 | 110 | Red | 44 | 76 | 1,200 |
| USH-A -100 | 70-OTHR0108 | 100 | 220 | 4 | 220 | Blue | 44 | 76 | 1,200 |
| USH-A -150 | 70-OTHR0109 | 150 | 330 | 6 | 330 | Yellow | 44 | 76 | 1,300 |
| USH-B -100 | N/A | 100 | 220 | 4 | 220 | Green | 60 | 105 | 1,800 |
| USH-B -150 | N/A | 150 | 330 | 6 | 330 | Brown | 60 | 105 | 1,800 |
| USH-B -200 | 70-OTHR0107 | 200 | 440 | 8 | 440 | White | 60 | 105 | 1,800 |
| USH-B -300 | N/A | 300 | 660 | 12 | 660 | Orange | 60 | 105 | 1,900 |
| USH-B -400 | N/A | 400 | 880 | 16 | 880 | Blue | 60 | 105 | 2,000 |
| USH-C -350 | N/A | 350 | 770 | 14 | 770 | Black | 73 | 105 | 2,500 |
| USH-C -500 | N/A | 500 | 1100 | 20 | 1100 | Green | 73 | 105 | 2,600 |
| USH-C -600 | N/A | 600 | 1320 | 24 | 1320 | Orange | 73 | 105 | 2,800 |
| USH-C -750 | N/A | 750 | 1650 | 30 | 1650 | Brown | 73 | 105 | 2,800 |